

Uni-Base

UB 135x135x156 29.5 15 G

Číslo dílu...:10.01.15.00571

<https://www.schmalz.com/10.01.15.00571>

Domovská stránka > Technologie vakuového upínání > Clamping Equipment for 3D Freeform Surfaces > Clamping Equipment for Manual Processing > Basic Holding Fixture BHF > UB 135x135x156 29.5 15 G

Uni-Base, flexibly adjustable



Length L: 135 mm

Width B: 135 mm


Height H: 156 mm

Stroke Z: 29,5 mm

Slewing angle W: 15 °

Construction use: smooth table

Údaje o konstrukci



Atribut	Wert
B	135 mm
D	60,50 mm
D1	6 mm
D2	8 mm
H	156 mm
L	135 mm
W	15 °
Z (Stroke)	29,50 mm

Příslušenství

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Uni-Base

UB 135x135x156 29.5 15 G

Číslo dílu...:10.01.15.00571

<https://www.schmalz.com/10.01.15.00571>



SSCB-78 93.5-107.5 ZP 60 SAB-NBR

Číslo dílu...:10.01.15.00572

Pitch diameter D mk: 78 mm

Function Suction cup: Jointly controlled Pins

Suct. cups: Bellows suct. cup SAB

Connection: Ø60mm

Material: NBR

Material hardness [Shore A]: 60 Shore A

Material: NBR

Height H1: 117,3 mm



ISCUP Cup 1 80x80x30

Číslo dílu...:10.01.15.00003

Dimensions (LxB): 80 x 80

Length L: 80 mm

Width B: 80 mm

Height H: 30 mm



ISCUP Cup 2 80x40x30

Číslo dílu...:10.01.15.00004

Dimensions (LxB): 80 x 40

Length L: 80 mm

Width B: 40 mm

Height H: 30 mm

Uni-Base

UB 135x135x156 29.5 15 G

Číslo dílu...:10.01.15.00571

<https://www.schmalz.com/10.01.15.00571>



ISCUP Cup 3 80x28x30

Číslo dílu...:10.01.15.00005

Dimensions (LxB): 80 x 28

Length L: 80 mm

Width B: 28 mm

Height H: 30 mm



SSPB-117 117-125 NBR

Číslo dílu...:10.01.15.00719

Diameter Ds: 117 mm

Height H1: 137 mm

Stroke Z: 8 mm

Material: ED

Sealing material: Perbunan



RSC 85x120-VU1-40-IS-BHF

Číslo dílu...:10.01.15.00587

Height H: 99 mm

Height H1: 120 mm

Stroke Z: 21 mm

Suction cup material: Vulkollan VU1

Suct. cups: Innospann

Construction use: Basic Holding Fixture