

Plug union, elbow

STV-W G1/4-AG 6

Číslo dílu...:10.08.02.00462

<https://www.schmalz.com/10.08.02.00462>

Domovská stránka > Screw in Push Fittings > STV-W G1/4-AG 6

Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 6 mm

Material: Plastic

Operating temperature: 0 ... 60 °C

Length L: 19,5 mm

Údaje o konstrukci



Atribut	Wert
d	6 mm
G1	G1/4"-M
dn	6 mm
D1	14 mm
H	10,70 mm
H1	17,10 mm
L	19,50 mm
L1	27,50 mm
LG1	6 mm
SW1	16 mm

Technické údaje

Atribut	Wert
Hose type	Hose D = 6 d = 4
Hose type	6-4
Material	Plastic
Pressure range (operating pressure)	-0.95 ... 10.00 bar
Operating temperature	0 ... 60 °C
Weight	19,30 g
Product family	STV

[Kontaktujte společnost Schmalz](#)

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 2

Plug union, elbow

STV-W G1/4-AG 6

Číslo dílu...:10.08.02.00462

<https://www.schmalz.com/10.08.02.00462>
