

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Mounting Elements > Spring Plungers > Spring Plungers FSTE-HDB > FSTE-HDB G1/8-AG 45 VG-AB

Spring plunger with damping and height compensation, heavy-duty and ball guided anti-rotation guard




Suction cup connection: G1/8"-M

Vacuum connection: G1/8"-F

Spring stroke Z: 45 mm

Shape mounting elements: Rotation lock anti-block

Údaje o konstrukci



Atribut	Wert
G1	G1/8"-F
G2	G1/8"-M
G3	M16x1-M
H	130,50 mm
H2	52,50 mm
LG1	7 mm
LG2	8,50 mm
LG3	34 mm
SW1	22 mm
SW2	12 mm
SW3	19 mm
Z (Stroke)	45 mm

Recommendation: Avoid maximum plunger stroke Z during continuous operation to extend service life Ensure that the hose guide is free from distortion

Technické údaje

Atribut	Wert
Shape mounting elements	Rotation lock anti-block
Spring rate	0,10 N/mm
Spring pretension	3,59 N
Spring force, center	5,77 N

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>

Vertical load	3700 N
Horizontal load	173 N
Weight	149 g
Operating temperature	0 ... 80 °C
Product family	FSTE-HDB

Note: Spring force: Referred to 50 % of operating stroke Vertical load: Maximum static loading Horizontal load: The specification of the horizontal load refers to the lower edge of the plunger with extended spring. It is a maximum static stress and it impairs the spring compression and extension in horizontal position.

Příslušenství



HTR-UNI 2N FSTE-HDB

Číslo dílu...:10.01.03.00332

Operating temperature: °C

Shape: for FSTE-HDB

Cross-beam connection: 2 T-slots



KGL G1/8-IG G1/8-AG A2

Číslo dílu...:10.01.03.00109

Thread G1: G1/8"-F

Thread G2: G1/8"-M

Height H: 26,5 mm

Material: Aust. Stainless steel

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



HTR-STA 47 1N D10/16 FL


Číslo dílu...:10.08.03.00085

Length L: 47 mm

Connection 1: Sliding block

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: flat



HTR-STS 30x30 D10/16 WI

Číslo dílu...:10.08.03.00088

Connection 1: 30x30

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: angled



HTR-STS 40x40 D10/16 WI

Číslo dílu...:10.08.03.00089

Connection 1: 40x40

Connection of suction cup, spring plunger: Contour D10 and D16

Shape: angled

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



ST G1/8-AG 4 MS-ROH

Číslo dílu...:10.08.03.00153

Thread G1: G1/8"-M

Hose diameter (rec.) d: 4 mm

Material: Brass

Surface: raw

Length L: 4 mm

Nominal diameter dn: 2,5 mm



ST G1/8-AG 6 MS-V

Číslo dílu...:10.08.03.00154

Thread G1: G1/8"-M

Hose diameter (rec.) d: 6 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4,4 mm



ST G1/8-AG 9 MS-V

Číslo dílu...:10.08.03.00155

Thread G1: G1/8"-M

Hose diameter (rec.) d: 9 mm

Material: Brass

Surface: nickel plated

Length L: 5 mm

Nominal diameter dn: 4 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-GE G1/8-AG 4

Číslo dílu...:10.08.02.00202

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 7,9 mm

Length L: 13,7 mm



STV-GE G1/8-AG 6

Číslo dílu...:10.08.02.00204

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,4 mm

Length L: 16,4 mm



STV-GE G1/8-AG 8

Číslo dílu...:10.08.02.00206

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

External diameter D: 14 mm

Length L: 20,7 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-W G1/8-AG 4

Číslo dílu...:10.08.02.00156

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 16,4 mm



STV-W G1/8-AG 6

Číslo dílu...:10.08.02.00158

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 20,1 mm



STV-W G1/8-AG 8

Číslo dílu...:10.08.02.00160

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 24 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-GE G1/8-AG 6 HT

Číslo dílu...:10.08.02.00389

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

External diameter D: 11,6 mm

Length L: 19 mm



STV-W G1/8-AG 6

Číslo dílu...:10.08.02.00288

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Plastic

Operating temperature: °C

Length L: 20,8 mm



STV-W G1/8-AG 6 HT

Číslo dílu...:10.08.02.00391

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 120 °C

Length L: 22,5 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-WF G1/8-AG 4

Číslo dílu...:10.08.02.00166

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 17,4 mm



STV-WF G1/8-AG 6

Číslo dílu...:10.08.02.00168

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 21,4 mm



STV-WF G1/8-AG 8

Číslo dílu...:10.08.02.00170

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 23,4 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-WF G1/8-AG 10

Číslo dílu...:10.08.02.00257

Thread G1: G1/8"-M

Hose diameter: 10 mm

Material: Nickel plated

Operating temperature: -10 ... 70 °C

Length L: 25,2 mm



STV-T G1/8-AG 4

Číslo dílu...:10.09.02.00039

Thread G1: G1/8"-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

Length L: 32,5 mm



STV-T G1/8-AG 6

Číslo dílu...:10.09.02.00040

Thread G1: G1/8"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41,5 mm

Spring plungers

FSTE-HDB G1/8-AG 45 VG-AB

Číslo dílu...:10.01.02.01439

<https://www.schmalz.com/10.01.02.01439>



STV-T G1/8-AG 8

Číslo dílu...:10.09.02.00041

Thread G1: G1/8"-M

Hose diameter: 8 mm

Material: Brass

Operating temperature: °C

Length L: 48,7 mm