

Suspension, fixable

FST-C 100-HD1-L

Číslo dílu...:10.01.20.01501

<https://www.schmalz.com/10.01.20.01501>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Mounting Elements > Suspension Clampable FST-C > FST-C 100-HD1-L

Suspension with height compensation and pneumat. clamping heavy-duty



Shape mounting elements: Heavy Duty 1 sp. plug

Spring stroke Z: 100 mm

Weight: 10,8 kg


Length L: 170 mm

Width B: 170 mm

Height H: 50 mm

Construction use: Large-area vacuum gripper

Údaje o konstrukci



Atribut	Wert
B	170 mm
B1	431,90 mm
B2	45 mm
H	50 mm
H1	120 mm
L	170 mm
L1	250 mm
L2	220 mm
Z (Stroke)	100 mm

Příslušenství

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Suspension, fixable

FST-C 100-HD1-L

Číslo dílu...:10.01.20.01501

<https://www.schmalz.com/10.01.20.01501>



EMV 5 24V-DC 3/2 NO

Číslo dílu...:10.05.01.00068

Nominal size: 5 mm

Voltage DC: 24V - DC

Function: 3/2-way valve

Control valve: Normally open

Connecting thread: G1/4"-F

Pressure range (operating pressure): bar

Power consumption DC: 8 W



PROP-VENT 24V-DC DC

Číslo dílu...:10.05.05.00104

Thread G1: G1/8"-F

Voltage: 24V - DC

Current type: Direct current



STV-GE G1/4-AG 6

Číslo dílu...:10.08.02.00205

Thread G1: G1/4"-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: -20 ... 80 °C

External diameter D: 11,2 mm

Length L: 15,2 mm