

Vacuum/pressure sensor

VS VP8 SA M8-4

Číslo dílu...:10.06.02.00562

<https://www.schmalz.com/10.06.02.00562>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Switches and System Monitoring > Vacuum and Pressure Sensors > Vacuum and Pressure Sensors VS > VS VP8 SA M8-4

Vacuum/pressure sensor without display




Measuring range: -1...8bar

Construction shape vacuum switch: Analog sensor

Electrical connection: Male connect M8, 4 pole

Údaje o konstrukci



Atribut	Wert
D	19,60 mm
G1	G1/8"-M
G2	M5-F
G3	M8x1-M
L	38 mm
L1	55 mm
LG1	8 mm

Technické údaje

Atribut	Wert
Measured medium	Non-aggressive gases; dry, oil-free air
Measuring range	-1,0 ... 8,0 bar
Overpressure resistance	12 bar
Repeatability	± 3% of full-scale value
Electrical connection	Male connect M8, 4 pole
Connection	G1/8"-M + M5-F
Voltage	15-30V DC
Current consumption	10 mA

[Kontaktujte společnost Schmalz](#)

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 3

Vacuum/pressure sensor

VS VP8 SA M8-4

Číslo dílu...:10.06.02.00562

<https://www.schmalz.com/10.06.02.00562>

Protection type IP	IP 65
Temperature influence	± 3% of full-scale value
Operating temperature	0 ... 50 °C
Weight	12 g
Measuring range	-14.5 ... 116.0 psi psi
Overpressure resistance	174,04 psi
Inputs/outputs	Analog: 0...10 V
Product family	VS

Příslušenství



ASK B-M8-4 3000 K-4P

Číslo dílu...:10.06.02.00472

Electrical connection: Fem connect M8, 4 pol

Cable length: 3 000 mm

Material hose: PUR cable



BEF-WIN 21x22x60.5 1.5 VS

Číslo dílu...:10.06.02.00061

Length L: 60,5 mm

Width B: 21 mm

Height H: 22 mm

Wall thickness s: 1,5 mm

Construction use: Vacuum switch

Vacuum/pressure sensor

VS VP8 SA M8-4

Číslo dílu...:10.06.02.00562

<https://www.schmalz.com/10.06.02.00562>



HTR-VSi Clip

Číslo dílu...:10.06.02.00718

Width B: 12 mm

Height H: 25,3 mm

Length L: 20 mm

Construction use: Vacuum/pressure switch