

## Bellows suction cup (round)

FG 7 NBR-ESD-55 N062

Číslo dílu...:10.01.06.04139

<https://www.schmalz.com/10.01.06.04139>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FG 7 NBR-ESD-55 N062

### Bellows suction cup (round) for very uneven workpieces




Size: 7

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5

### Údaje o konstrukci



| Atribut    | Wert    |
|------------|---------|
| d          | 4,50 mm |
| d2         | 1,80 mm |
| D1         | 6,50 mm |
| Dk         | 9 mm    |
| Dmax(S)    | 7 mm    |
| Ds         | 5,90 mm |
| H          | 14 mm   |
| H2         | 3,80 mm |
| H3         | 6,50 mm |
| Z (Stroke) | 3 mm    |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technické údaje

| Atribut                     | Wert                   |
|-----------------------------|------------------------|
| Suction force (-600mbar)    | 0,15 N                 |
| Pull-off force              | 0,90 N                 |
| Volume                      | 0,16 cm <sup>3</sup>   |
| Curve radius (min) (convex) | 7,50 mm                |
| Size                        | 7                      |
| Number of folds             | 2,50                   |
| Suction cup material        | Nitrile rubber NBR-ESD |

**Kontaktujte společnost Schmalz**

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | [schmalz@schmalz.cz](mailto:schmalz@schmalz.cz)

## Bellows suction cup (round)

FG 7 NBR-ESD-55 N062

Číslo dílu...:10.01.06.04139

<https://www.schmalz.com/10.01.06.04139>

Material hardness [Shore A]

55 Shore A

Weight

0,50 g

Product family

FG

### Příslušenství



#### SA-NIP N062 M5-AG DN250

Číslo dílu...:10.01.06.05668

Thread G1: M5-M

Length L1: 15,9 mm

Fitting length: 5 mm

Nominal diameter dn: 2,5 mm

Material: Aluminum



#### SA-NIP N062 G1/8-IG DN350

Číslo dílu...:10.01.06.05669

Thread G1: G1/8"-F

Length L1: 17,9 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



#### SA-NIP N062 G1/8-AG DN350

Číslo dílu...:10.01.06.05670

Thread G1: G1/8"-M

Length L1: 19,4 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

## Bellows suction cup (round)

FG 7 NBR-ESD-55 N062

Číslo dílu...:10.01.06.04139

<https://www.schmalz.com/10.01.06.04139>

---