

Bellows suction cups (round)

FSG 42 NBR-55 G1/4-AG

Číslo dílu...:10.01.06.00031

<https://www.schmalz.com/10.01.06.00031>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 42 NBR-55 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



Size: 42

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A


Nipple material: Aluminum

Connection: G1/4"-M

Number of folds: 2,5

Vacuum connection: G1/4"-M

Údaje o konstrukci



Atribut	Wert
d2	17,80 mm
dn	4,40 mm
Dmax(S)	45 mm
Ds	42,60 mm
G1	G1/4"-M
H	50 mm
LG1	11 mm
SW1	17 mm
Z (Stroke)	20 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	42
Number of folds	2,50
Connection	G1/4-AG
Curve radius (min) (convex)	75 mm
Volume	19,79 cm ³

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

FSG 42 NBR-55 G1/4-AG

Číslo dílu...:10.01.06.00031

<https://www.schmalz.com/10.01.06.00031>

Suction force (-600mbar)	14,93 N
Pull-off force	44 N
Hose diameter (rec.) d	6 mm
Weight	27 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



DR 42/20x5 MOS SI-15

Číslo dílu...:10.01.06.02616

External diameter D: 42 mm

Internal diameter d: 20 mm

Height H: 5 mm

Material type: Foam rubber

Sealing material: Silicone SI

Material hardness [Shore A]: 15 Shore A



FD 34 120

Číslo dílu...:10.01.06.02572

External diameter D: 34 mm

Filter pore size: 120 µm

Construction use: Bellows suction cup

Size: FG 42

Bellows suction cups (round)

FSG 42 NBR-55 G1/4-AG

Číslo dílu...:10.01.06.00031

<https://www.schmalz.com/10.01.06.00031>



SU 40

Číslo dílu...:10.01.01.12856

Size: 40

Clamping range: 35.0 ... 45.0 mm

Temperature resistance: 80 °C

Náhradní díly



SA-NIP N018 G1/4-AG DN440

Číslo dílu...:10.01.06.01065

Nipple family: N 018

Thread G1: G1/4"-M

Length L1: 28,8 mm

Fitting length: 4 mm

Nominal diameter dn: 4,4 mm

Spanner size SW2: 5 mm

Material: Aluminum



FG 42 NBR-55 N018

Číslo dílu...:10.01.06.00141

Size: 42

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5