

Bellows suction cups (round)

FSG 25 NBR-55 G1/8-AG

Číslo dílu...:10.01.06.00334

<https://www.schmalz.com/10.01.06.00334>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > Bellows Suction Cups FSG (2.5 Folds) > FSG 25 NBR-55 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Connection: G1/8"-M

Number of folds: 2,5

Vacuum connection: G1/8"-M

Údaje o konstrukci



Atribut	Wert
d2	10 mm
dn	3,50 mm
Dmax(S)	26 mm
Ds	23 mm
G1	G1/8"-M
H	40 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	18 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Size	25
Number of folds	2,50
Connection	G1/8-AG
Curve radius (min) (convex)	30 mm
Volume	5,40 cm ³

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

FSG 25 NBR-55 G1/8-AG

Číslo dílu...:10.01.06.00334

<https://www.schmalz.com/10.01.06.00334>

Suction force (-600mbar)	4,71 N
Pull-off force	19 N
Hose diameter (rec.) d	4 mm
Weight	8 g
Product family	FSG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Pull-off force: The pull-off force of the versions made of natural rubber is reduced by about 40% Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



DR 22.5/13x2 MOS SI-15

Číslo dílu...:10.01.06.02614

External diameter D: 22,5 mm

Internal diameter d: 13 mm

Height H: 2 mm

Material type: Foam rubber

Sealing material: Silicone SI

Material hardness [Shore A]: 15 Shore A



FD 18 120

Číslo dílu...:10.01.06.02567

External diameter D: 18 mm

Filter pore size: 120 µm

Construction use: Bellows suction cup

Size: FG25/FGA25

Bellows suction cups (round)

FSG 25 NBR-55 G1/8-AG

Číslo dílu...:10.01.06.00334

<https://www.schmalz.com/10.01.06.00334>



SPI 25 PEEK

Číslo dílu...:10.01.06.03286

Size: 25

Material: Polyetheretherketon

Náhradní díly



SA-NIP N016 G1/8-AG DN350

Číslo dílu...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



FG 25 NBR-55 N016

Číslo dílu...:10.01.06.00335

Size: 25

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Number of folds: 2,5