

Flat suction cup (oval)

SGON 24x8 SI-HD-65 G1/8-AG

Číslo dílu...:10.01.05.01052

<https://www.schmalz.com/10.01.05.01052>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > Flat Suction Cups SGON > SGON 24x8 SI-HD-65 G1/8-AG

Flat suction cup (oval) for long and also curved workpieces




Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Nipple material: Aluminum

Connection: G1/8"-M

Údaje o konstrukci



Atribut	Wert
Bmax(S)	9 mm
Bs	8 mm
dn	1,50 mm
G1	G1/8"-M
H	17 mm
LG1	8 mm
Lmax(S)	24,50 mm
Ls	24 mm
SW1	14 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for rubber parts concerning to DIN ISO 3302-1 M3.

Technické údaje

Atribut	Wert
Suction force (-600mbar)	8 N
Volume	0,33 cm ³
Curve radius (min) (convex)	7,50 mm
Hose diameter (rec.) d	4 mm
Number of folds	0
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (oval)

SGON 24x8 SI-HD-65 G1/8-AG

Číslo dílu...:10.01.05.01052

<https://www.schmalz.com/10.01.05.01052>

Weight	6,70 g
Product family	SGON

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SGO 24x8 SI-HD-65 N022

Číslo dílu...:10.01.05.01036

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A



SA-NIP N022 G1/8-AG DN350

Číslo dílu...:10.01.05.00124

Thread G1: G1/8"-M

Length L1: 18,5 mm

Fitting length: 5 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum

Flat suction cup (oval)

SGON 24x8 SI-HD-65 G1/8-AG

Číslo dílu...:10.01.05.01052

<https://www.schmalz.com/10.01.05.01052>



SA-NIP N022 G1/8-IG DN350

Číslo dílu...:10.01.05.00123

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 13 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



ZOKL 11-13

Číslo dílu...:10.07.10.00032

Clamping range: 11.0 ... 13.0 mm

Material: Galvanized steel