

Flat suction cup (round)

PFG 1 NBR-55 N001

Číslo dílu...:10.01.01.00001

<https://www.schmalz.com/10.01.01.00001>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 1 NBR-55 N001

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 1

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Údaje o konstrukci



Atribut	Wert
d	0,80 mm
Dk	1,20 mm
Dmax(S)	1,20 mm
Ds	1 mm
H	1,60 mm
Z (Stroke)	0,10 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	0,03 N
Volume	0,00 cm ³
Curve radius (min) (convex)	2 mm
Size	1
Nipple family	N 001
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

PFG 1 NBR-55 N001

Číslo dílu...:10.01.01.00001

<https://www.schmalz.com/10.01.01.00001>

Weight

0 g

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SA-NIP N001 M3-AG DN40

Číslo dílu...:10.01.01.00315

Thread G1: M3-M

Length L1: 6 mm

Fitting length: 2 mm

Material: Aluminum