

Flat suction cup (round)

PFG 50 NBR-55 N008

Číslo dílu...:10.01.01.00017

<https://www.schmalz.com/10.01.01.00017>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 50 NBR-55 N008

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 50

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Údaje o konstrukci



Atribut	Wert
d	8 mm
d1	20 mm
Dk	29,10 mm
Dmax(S)	53,50 mm
Ds	50 mm
H	15 mm
H2	7 mm
Z (Stroke)	4 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	91 N
Volume	7,08 cm ³
Curve radius (min) (convex)	75 mm
Size	50
Nipple family	N 008
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

PFG 50 NBR-55 N008

Číslo dílu...:10.01.01.00017

<https://www.schmalz.com/10.01.01.00017>

Weight	10,20 g
Product family	PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SA-NIP N008 G1/8-AG DN350

Číslo dílu...:10.01.01.03532

Thread G1: G1/8"-M

Length L1: 22 mm

Fitting length: 5 mm

Material: Aluminum

Spanner size SW2: 4 mm



SA-NIP N008 G1/8-IG DN350

Číslo dílu...:10.01.01.03524

Thread G1: G1/8"-F

Length L1: 25 mm

Fitting length: 16 mm

Material: Aluminum

Spanner size SW2: 4 mm

Flat suction cup (round)

PFG 50 NBR-55 N008

Číslo dílu...:10.01.01.00017

<https://www.schmalz.com/10.01.01.00017>



SU 50

Číslo dílu...:10.01.01.12837

Size: 50

Clamping range: 45.0 ... 60.0 mm

Temperature resistance: 80 °C