

Flat suction cup (round)

PFYN 8 FPM-65 M5-AG

Číslo dílu...:10.01.01.00181

<https://www.schmalz.com/10.01.01.00181>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 8 FPM-65 M5-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 8

Suction cup material: Fluorocaotchuc FPM


Material hardness [Shore A]: 65 Shore A

Material property: non-marking

Nipple material: Aluminum

Vacuum connection: M5-M

Údaje o konstrukci



Atribut

Wert

dn	2 mm
Dmax(S)	9 mm
Ds	8 mm
G1	M5-M
H	12 mm
LG1	4,50 mm
SW1	8 mm
Z (Stroke)	1,30 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	2,30 N
Volume	0,03 cm ³
Curve radius (min) (convex)	10 mm
Hose diameter (rec.) d	2 mm
Size	8
Suction cup material	Fluorocaotchuc FPM
Material hardness [Shore A]	65 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

PFYN 8 FPM-65 M5-AG

Číslo dílu...:10.01.01.00181

<https://www.schmalz.com/10.01.01.00181>

Weight 1,20 g

Product family PFYN

Number of folds 0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SA-NIP N004 M5-AG DN200

Číslo dílu...:10.01.01.03526

Thread G1: M5-M

Length L1: 13,5 mm

Fitting length: 5 mm

Material: Aluminum