

Flat suction cup (round)

PFYN 10 SI-CO-55 G1/8-IG

Číslo dílu...:10.01.01.10361

<https://www.schmalz.com/10.01.01.10361>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN > PFYN 10 SI-CO-55 G1/8-IG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 10

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-F

Údaje o konstrukci



Atribut	Wert
dn	2 mm
Dmax(S)	11,50 mm
Ds	10 mm
G1	G1/8"-F
H	23,50 mm
LG1	9 mm
SW1	14 mm
Z (Stroke)	1,40 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	4 N
Volume	0,07 cm ³
Curve radius (min) (convex)	12,50 mm
Hose diameter (rec.) d	4 mm
Size	10
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

PFYN 10 SI-CO-55 G1/8-IG

Číslo dílu...:10.01.01.10361

<https://www.schmalz.com/10.01.01.10361>

Weight	5,30 g
Product family	PFYN
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SA-NIP N004 G1/8-IG DN200

Číslo dílu...:10.01.01.03520

Thread G1: G1/8"-F

Length L1: 20 mm

Fitting length: 16 mm

Material: Aluminum



PFG 10 SI-CO-55 N004

Číslo dílu...:10.01.01.00701

Size: 10

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A