

Flat suction cup (round)

PFYN 15 VU1-72 G1/8-AG

Číslo dílu...:10.01.01.00556

<https://www.schmalz.com/10.01.01.00556>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups PFYN VU1 > PFYN 15 VU1-72 G1/8-AG

Flat suction cup (round) for smooth or slightly rough surfaces



Size: 15


Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A

Nipple material: Aluminum

Connection: G1/8"-M

Údaje o konstrukci



Atribut	Wert
Dmax(S)	17,50 mm
dn	2 mm
Ds	14,50 mm
G1	G1/8"-M
H	14,50 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	1,50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Size	15
Suction cup material	Vulkollan VU1
Suction force (-600mbar)	8,50 N
Volume	0,50 cm ³
Curve radius (min) (convex)	12,50 mm
Hose diameter (rec.) d	4 mm
Nipple family	N 005

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 2

Flat suction cup (round)

PFYN 15 VU1-72 G1/8-AG

Číslo dílu...:10.01.01.00556

<https://www.schmalz.com/10.01.01.00556>

Material hardness [Shore A]	72 Shore A
Weight	6,40 g
Number of folds	0
Product family	PFYN

Note: Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3

Náhradní díly



SA-NIP N005 G1/8-AG DN200

Číslo dílu...:10.01.01.03529

Nipple family: N 005

Thread G1: G1/8"-M

Length L1: 17,5 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum



PFG 15 VU1-72 N005

Číslo dílu...:10.01.01.00555

Size: 15

Suction cup material: Vulkollan VU1

Material hardness [Shore A]: 72 Shore A