

Flat suction cup (round)

SUF 5 SI-CO-55 M5-IG

Číslo dílu...:10.01.01.14245

<https://www.schmalz.com/10.01.01.14245>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > Flat Suction Cups SUF > SUF 5 SI-CO-55 M5-IG

Flat suction cup (round) for process safe handling of smooth or slightly rough surfaces




Size: 5

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A

Vacuum connection: M5-F

Údaje o konstrukci



Atribut	Wert
Dmax(S)	5,70 mm
Ds	5 mm
dn	1,80 mm
G1	M5-F
H	14,20 mm
LG1	5,50 mm
SW1	8 mm
Z (Stroke)	0,50 mm

Technické údaje

Atribut	Wert
Suction force (-600mbar)	0,90 N
Pull-off force	0,90 N
Volume	0,01 cm ³
Curve radius (min) (convex)	8 mm
Hose diameter (rec.) d	2 mm
Size	5
Suction cup material	Silicone SI conductive
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 2

Flat suction cup (round)

SUF 5 SI-CO-55 M5-IG

Číslo dílu...:10.01.01.14245

<https://www.schmalz.com/10.01.01.14245>

Weight	1,10 g
Product family	SUF
Number of folds	0

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SC 020 M5-IG

Číslo dílu...:10.01.06.04306

Connection geometry: 020

Vacuum connection: M5-F

Fitting length: 8,7 mm

Nominal diameter dn: 1,8 mm



SUF 5 SI-CO-55 SC020

Číslo dílu...:10.01.01.14023

Size: 5

Suction cup material: Silicone SI conductive

Material hardness [Shore A]: 55 Shore A