

Flat suction cup (round)

SUF 18 NBR-55 SC030

Číslo dílu...:10.01.01.13946

<https://www.schmalz.com/10.01.01.13946>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SUF 18 NBR-55 SC030

Flat suction cup (round) f. process- safe handling of smooth or slightly rough surfaces




Size: 18

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Údaje o konstrukci



Atribut	Wert
d1	7,30 mm
d	5,30 mm
Dk	11,50 mm
Dmax(S)	20,60 mm
Ds	18 mm
H	9,30 mm
H2	4,30 mm
H3	5,80 mm
Z (Stroke)	1,80 mm

Technické údaje

Atribut	Wert
Suction force (-600mbar)	13 N
Pull-off force	13 N
Volume	0,37 cm ³
Curve radius (min) (convex)	20 mm
Size	18
Nipple family	SC030
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SUF 18 NBR-55 SC030

Číslo dílu...:10.01.01.13946

<https://www.schmalz.com/10.01.01.13946>

Weight	1,10 g
Product family	SUF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a smooth, dry workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SC 030 G1/8-AG

Číslo dílu...:10.01.06.04288

Connection geometry: 030

Vacuum connection: G1/8"-M

Fitting length: 6 mm

Nominal diameter dn: 3,1 mm



SC 030 G1/8-IG

Číslo dílu...:10.01.06.04307

Connection geometry: 030

Vacuum connection: G1/8"-F

Fitting length: 14 mm

Nominal diameter dn: 3,1 mm