

## Flat suction cup (oval)

SAOF 80x40 NBR-60 G1/4-AG

Číslo dílu...:10.01.05.00314

<https://www.schmalz.com/10.01.05.00314>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal > Flat Suction Cups SAOF (Oval) > SAOF 80x40 NBR-60 G1/4-AG

### Flat suction cup (oval) for very dynamic handling of smooth and oily workpieces



Dimensions (LxB): 80x40


Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 60 Shore A

Nipple material: Aluminum

Connection: G1/4-AG

### Údaje o konstrukci



| Atribut    | Wert     |
|------------|----------|
| Bmax(S)    | 43 mm    |
| Bs         | 38,60 mm |
| dn         | 5 mm     |
| G1         | G1/4"-M  |
| H          | 20 mm    |
| LG1        | 8 mm     |
| Lmax(S)    | 85 mm    |
| Ls         | 80,60 mm |
| SW1        | 17 mm    |
| Z (Stroke) | 4 mm     |

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

### Technické údaje

| Atribut                      | Wert                  |
|------------------------------|-----------------------|
| Suction force (-600mbar)     | 140 N                 |
| Lateral force                | 110 N                 |
| Lateral force (oily surface) | 100 N                 |
| Volume                       | 11,70 cm <sup>3</sup> |
| Curve radius (min) (convex)  | 50 mm                 |
| Hose diameter (rec.) d       | 4 mm                  |
| Number of folds              | 0                     |

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | [schmalz@schmalz.cz](mailto:schmalz@schmalz.cz)

Stránka 1 z 2

## Flat suction cup (oval)

SAOF 80x40 NBR-60 G1/4-AG

Číslo dílu...:10.01.05.00314

<https://www.schmalz.com/10.01.05.00314>

|                             |                    |
|-----------------------------|--------------------|
| Suction cup material        | Nitrile rubber NBR |
| Material hardness [Shore A] | 60 Shore A         |
| Weight                      | 34 g               |
| Product family              | SAOF               |
| Dimensions (LxB)            | 80x40              |

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Lateral force: The specified lateral forces are values measured at a vacuum of -0.6 bar with a dry or oily, smooth, flat workpiece surface. Depending on the workpiece surface and its quality, the actual values may deviate from these values Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m