

Flat suction cup (round)

SGPN 15 NK-40 G1/8-IG

Číslo dílu...:10.01.01.10181

<https://www.schmalz.com/10.01.01.10181>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 15 NK-40 G1/8-IG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 15


Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A

Nipple material: Aluminum

Vacuum connection: G1/8"-F

Údaje o konstrukci



Atribut	Wert
dn	3,50 mm
Dmax(S)	15,50 mm
Ds	14,50 mm
G1	G1/8"-F
H	22 mm
LG1	8 mm
SW1	14 mm
Z (Stroke)	0,90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	5,50 N
Volume	0,28 cm ³
Hose diameter (rec.) d	2 mm
Size	15
Number of folds	0
Suction cup material	Natural Rubber NK
Material hardness [Shore A]	40 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SGPN 15 NK-40 G1/8-IG

Číslo dílu...:10.01.01.10181

<https://www.schmalz.com/10.01.01.10181>

Weight	4,50 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SA-NIP N016 G1/8-IG DN350

Číslo dílu...:10.01.06.05731

Nipple family: N 016

Thread G1: G1/8"-F

Length L1: 18,5 mm

Fitting length: 12 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SGP 15 NK-40 N016

Číslo dílu...:10.01.01.10318

Size: 15

Suction cup material: Natural Rubber NK

Material hardness [Shore A]: 40 Shore A