

Flat suction cup (round)

SGPN 24 SI-50 G1/8-AG

Číslo dílu...:10.01.01.11987

<https://www.schmalz.com/10.01.01.11987>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 24 SI-50 G1/8-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 24

Suction cup material: Silicone SI


Material hardness [Shore A]: 50 Shore A

Nipple material: Aluminum

Material characteristics: FDA

Vacuum connection: G1/8"-M

Údaje o konstrukci



Atribut	Wert
dn	3,50 mm
Dmax(S)	25,50 mm
Ds	24 mm
G1	G1/8"-M
H	16,80 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	1,70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	11 N
Volume	0,85 cm ³
Hose diameter (rec.) d	4 mm
Size	24
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SGPN 24 SI-50 G1/8-AG

Číslo dílu...:10.01.01.11987

<https://www.schmalz.com/10.01.01.11987>

Weight	5,20 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Náhradní díly



SA-NIP N016 G1/8-AG DN350

Číslo dílu...:10.01.06.05735

Nipple family: N 016

Thread G1: G1/8"-M

Length L1: 20 mm

Fitting length: 6 mm

Nominal diameter dn: 3,5 mm

Material: Aluminum



SGP 24 SI-50 N016

Číslo dílu...:10.01.01.10577

Size: 24

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A