

Bellows suction cups (round)

SPB1 60 ED-65 G1/4-AG

Číslo dílu...:10.01.06.03502

<https://www.schmalz.com/10.01.06.03502>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB1 (1.5 Folds) > SPB1 60 ED-65 G1/4-AG

Bellows suction cup (round) for very uneven workpieces



Size: 60


Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/4"-M

Number of folds: 1,5

Údaje o konstrukci



Atribut	Wert
d2	38,60 mm
dn	6,10 mm
Dmax(S)	69,60 mm
Ds	61,40 mm
G1	G1/4"-M
H	43,20 mm
LG1	10 mm
SW1	17 mm
Z (Stroke)	22 mm

Technické údaje

Atribut	Wert
Suction force (-600mbar)	78 N
Pull-off force	100,90 N
Lateral force	49,40 N
Volume	49,24 cm ³
Curve radius (min) (convex)	70 mm
Hose diameter (rec.) d	6 mm
Size	60
Number of folds	1,50

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

SPB1 60 ED-65 G1/4-AG

Číslo dílu...:10.01.06.03502

<https://www.schmalz.com/10.01.06.03502>

Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	33,20 g
Product family	SPB1

Příslušenství



SIEB 17.5x0.8 MS-A2 280 0.28/0.16

Číslo dílu...:10.07.01.00308

External diameter D: 17,5 mm

Length L: 0,8 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SC-SW 60 6

Číslo dílu...:10.05.04.00096

Spanner size SW1: 6 mm

Nominal size: 60

Bellows suction cups (round)

SPB1 60 ED-65 G1/4-AG

Číslo dílu...:10.01.06.03502

<https://www.schmalz.com/10.01.06.03502>



SC-SW 80 6

Číslo dílu...:10.05.04.00097

Spanner size SW1: 6 mm

Nominal size: 80



SC-SW 100 6

Číslo dílu...:10.05.04.00098

Spanner size SW1: 6 mm

Nominal size: 100



SC-SW 120 6

Číslo dílu...:10.05.04.00099

Spanner size SW1: 6 mm

Nominal size: 120

Bellows suction cups (round)

SPB1 60 ED-65 G1/4-AG

Číslo dílu...:10.01.06.03502

<https://www.schmalz.com/10.01.06.03502>



SC-SW 200 6

Číslo dílu...:10.05.04.00100

Spanner size SW1: 6 mm

Nominal size: 200



SC-SW 240 6

Číslo dílu...:10.05.04.00101

Spanner size SW1: 6 mm

Nominal size: 240

Náhradní díly



SC 050 G1/4-AG MOD

Číslo dílu...:10.01.06.02487

Connection geometry: 050

Connection: G1/4"-M

Length L1: 26,5 mm

Fitting length: 7,2 mm

Nominal diameter dn: 6,1 mm

Bellows suction cups (round)

SPB1 60 ED-65 G1/4-AG

Číslo dílu...:10.01.06.03502

<https://www.schmalz.com/10.01.06.03502>



SPB1 60 ED-65 SC050

Číslo dílu...:10.01.06.02457

Size: 60

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Number of folds: 1,5