

Bellows suction cups (round)

SPB2f 25 SI-55 G1/8-AG

Číslo dílu...:10.01.06.04316

<https://www.schmalz.com/10.01.06.04316>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > Bellows Suction Cups SPB2f (2.5 Folds) > SPB2f 25 SI-55 G1/8-AG

Bellows suction cup (round) for very uneven workpieces



Size: 25


Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Thread G1: G1/8"-M

Number of folds: 2,5

Údaje o konstrukci



Atribut	Wert
d2	8 mm
dn	4,10 mm
Dmax(S)	28 mm
Ds	25 mm
G1	G1/8"-M
H	31,30 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	9,80 mm

Technické údaje

Atribut	Wert
Suction force at -200 mbar	1 N
Suction force at -400 mbar	2 N
Suction force (-600mbar)	3 N
Volume	2,94 cm ³
Size	25
Number of folds	2,50
Suction cup material	Silicone SI
Material hardness [Shore A]	55 Shore A

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Bellows suction cups (round)

SPB2f 25 SI-55 G1/8-AG

Číslo dílu...:10.01.06.04316

<https://www.schmalz.com/10.01.06.04316>

Weight	7,10 g
Product family	SPB2f

Náhradní díly



SC 040 G1/8-AG

Číslo dílu...:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SPB2f 25 SI-55 SC040

Číslo dílu...:10.01.06.04226

Size: 25

Suction cup material: Silicone SI

Material hardness [Shore A]: 55 Shore A

Material characteristics: FDA-compatible

Number of folds: 2,5