

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Číslo dílu...:10.01.01.13242

<https://www.schmalz.com/10.01.01.13242>

Domovská stránka > Flat Suction Cups SPF > SPF 25 ED-65 G1/8-AG

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 25

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Thread G1: G1/8"-M

Údaje o konstrukci



Atribut	Wert
dn	4,10 mm
Dmax(S)	28 mm
Ds	26,40 mm
G1	G1/8"-M
H	17 mm
LG1	7,50 mm
SW1	14 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	22,70 N
Pull-off force	27,10 N
Lateral force	17 N
Volume	1,70 cm ³
Curve radius (min) (convex)	30 mm
Hose diameter (rec.) d	4 mm
Size	25
Number of folds	0

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Stránka 1 z 3

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Číslo dílu...:10.01.01.13242

<https://www.schmalz.com/10.01.01.13242>

Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	7,10 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SIEB 11x1 MS-A2 280 0.28/0.16

Číslo dílu...:10.07.01.00309

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm



SU 25

Číslo dílu...:10.01.01.13584

Size: 25

Clamping range: 25.0 ... 30.0 mm

Temperature resistance: 80 °C

Náhradní díly

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SPF 25 ED-65 G1/8-AG

Číslo dílu...:10.01.01.13242

<https://www.schmalz.com/10.01.01.13242>



SC 040 G1/8-AG

Číslo dílu...:10.01.06.02490

Connection geometry: 040

Connection: G1/8"-M

Length L1: 20,2 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SPF 25 ED-65 SC040

Číslo dílu...:10.01.01.12371

Size: 25

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 11 mm