

Flat suction cup (round)

SPF 20 ED-65 SC040

Číslo dílu...:10.01.01.12370

<https://www.schmalz.com/10.01.01.12370>

Domovská stránka > Vakuová technologie pro automatizaci > Vacuum Components > Vacuum Suction Cups > Suction Cups for the Packaging Industry > SPF 20 ED-65 SC040

Flat suction cup (round) for dynamic handling of cardboard and rigid packaging




Size: 20

Suction cup material: Elastodur ED

Material hardness [Shore A]: 65 Shore A

Height H: 11 mm

Údaje o konstrukci



Atribut	Wert
d	7,50 mm
d1	10,50 mm
Dk	15,10 mm
Dmax(S)	23,30 mm
Ds	21,40 mm
H	11 mm
H2	4,60 mm
Z (Stroke)	2 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technické údaje

Atribut	Wert
Suction force (-600mbar)	16 N
Pull-off force	19,20 N
Lateral force	10,50 N
Volume	1,13 cm ³
Curve radius (min) (convex)	20 mm
Hose diameter (rec.) d	4 mm
Size	20

Kontaktujte společnost Schmalz

Schmalz s.r.o. | Družstevní 2169, 75301 Hranice, Czech Republic | +420 581 621 021 | schmalz@schmalz.cz

Flat suction cup (round)

SPF 20 ED-65 SC040

Číslo dílu...:10.01.01.12370

<https://www.schmalz.com/10.01.01.12370>

Nipple family	SC 040
Number of folds	0
Suction cup material	Elastodur ED
Material hardness [Shore A]	65 Shore A
Weight	1,40 g
Product family	SPF

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor
Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Příslušenství



SC 040 NPT1/8-AG

Číslo dílu...:10.01.06.02541

Connection geometry: 040

Connection: NPT1/8-M

Length L1: 20,9 mm

Fitting length: 6 mm

Nominal diameter dn: 4,1 mm



SC 040 NPT1/8-IG

Číslo dílu...:10.01.06.02542

Connection geometry: 040

Connection: NPT1/8-F

Length L1: 20,7 mm

Fitting length: 14 mm

Nominal diameter dn: 4,1 mm

Flat suction cup (round)

SPF 20 ED-65 SC040

Číslo dílu...:10.01.01.12370

<https://www.schmalz.com/10.01.01.12370>



SIEB 11x1 MS-A2 280 0.28/0.16

Číslo dílu...:10.07.01.00309

External diameter D: 11 mm

Length L: 1 mm

Material: Brass / Stainless steel

Filter pore size: 280 µm