

Flat suction cup (round)

SHF 70 NK-45 M10x1.25-IG E MOS

Part no...:10.01.01.12215


<https://www.schmalz.com/10.01.01.12215>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > SHF 70 NK-45 M10x1.25-IG E MOS

Flat suction cup (round) for highly dynamic handling of wood



Design Data



Accessories

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction cup (round)

SHF 70 NK-45 M10x1.25-IG E MOS

Part no...:10.01.01.12215

<https://www.schmalz.com/10.01.01.12215>



RED-NIP G1/4-AG M10x1.25-AG AL

Part no...:10.01.01.12194

Thread G1: G1/4"-M

Material: Aluminum



SA-NIP N009 G1/4-IG DN440

Part no...:10.01.01.12192

Thread G1: G1/4"-F

Fitting length: 19.3 mm

Material: Aluminum



SIEB 14.5x1 MS-A2 0.103/0.15

Part no...:10.05.03.00023

External diameter D: 14.5 mm

Length L: 1 mm

Material: Brass / Stainless steel

Flat suction cup (round)

SHF 70 NK-45 M10x1.25-IG E MOS

Part no...:10.01.01.12215

<https://www.schmalz.com/10.01.01.12215>



TVN G1/4-AG 9 N009

Part no...:10.05.10.00065

Thread G1: G1/4"-M

Thread G2: M10x1.25-M

Spring stroke Z: 9 mm

Nipple: N 009

Spare parts



DR 46/36x5 S05 EPDM-15 KE

Part no...:10.01.06.01678

External diameter D: 46 mm

Internal diameter d: 36 mm

Height H: 5 mm

Material type: Foam S, Height 5 mm

Sealing material: EPDM

Material hardness [Shore A]: 15 Shore A

Add. function: Adhesive tape on one side