

Bellows suction cup (round)

FGA 22 NBR-ESD-55 N062

Part no.:10.01.06.04454

<https://www.schmalz.com/10.01.06.04454>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 22 NBR-ESD-55 N062

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 22

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	4.50 mm
d2	11.70 mm
D1	24.20 mm
Dk	10 mm
Dmax(S)	25 mm
Ds	21.50 mm
H	19 mm
H2	3.80 mm
H3	9.10 mm
Z (Stroke)	6 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	5.70 N
Size	22
Suction cup material	Nitrile rubber NBR-ESD
Weight	2.10 g
Curve radius (min) (convex)	25 mm
Product family	FGA

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Bellows suction cup (round)

FGA 22 NBR-ESD-55 N062

Part no.:10.01.06.04454

<https://www.schmalz.com/10.01.06.04454>

Accessories



SA-NIP N062 M5-AG DN250

Part no.:10.01.06.05668

Thread G1: M5-M

Length L1: 15.9 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum



SA-NIP N062 G1/8-IG DN350

Part no.:10.01.06.05669

Thread G1: G1/8"-F

Length L1: 17.9 mm

Fitting length: 12 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum



SA-NIP N062 G1/8-AG DN350

Part no.:10.01.06.05670

Thread G1: G1/8"-M

Length L1: 19.4 mm

Fitting length: 6 mm

Nominal diameter dn: 3.5 mm

Material: Aluminum

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at