

Bellows suction cup (round)

FGA 2 NBR-ESD-55 N003

Part no.:10.01.06.04520

<https://www.schmalz.com/10.01.06.04520>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Bellows Suction Cups (Round) > FGA 2 NBR-ESD-55 N003

Bellows suction cup (round) with optimal adaptation to uneven surfaces




Size: 2

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Number of folds: 1.5

Design Data



Attribute	Value
d	2 mm
d1	3 mm
d2	1.30 mm
D1	3.30 mm
Dk	4 mm
Dmax(S)	4 mm
Ds	1.90 mm
H	4.50 mm
H2	1.50 mm
H3	2.30 mm
Z (Stroke)	1 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Number of folds	1.50
Suction force (-600mbar)	0.08 N
Size	2
Suction cup material	Nitrile rubber NBR-ESD
Weight	0 g

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Bellows suction cup (round)

FGA 2 NBR-ESD-55 N003

Part no...:10.01.06.04520

<https://www.schmalz.com/10.01.06.04520>

Curve radius (min) (convex)	1 mm
-----------------------------	------

Product family	FGA
----------------	-----