

## Area Gripper


FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>

Home > Vacuum Technology for Automation > Vacuum Components > Area Gripping Systems and End Effectors > Vacuum Area Gripping System  
FXP/FMP > Area Gripping Systems FXP > FXP-S-SW90 1036 5R36 SPB2-20-P

### Vacuum area gripping system with integrated pneumatic vacuum generator and flow resistors



Length L: 1,036 mm

Width B: 130 mm

Arrangement: 5R36

Number of suction cells: 137

Add. function: 2x control valve vacuum/blow-off

Design: Multi-stage ejector SEMP

Construction shape vacuum switch: PNP switching

Voltage DC: 24V - DC


Nozzle diameter: 0.9 mm

Air consumption: 625 l/min

Weight: 6.5 kg

Product family: FXP

### Design Data



| Attribute  | Value    |
|------------|----------|
| B          | 130 mm   |
| B3         | 21.60 mm |
| H          | 83 mm    |
| H1         | 122 mm   |
| H2         | 33 mm    |
| H3         | 7.70 mm  |
| H4         | 5.50 mm  |
| H5         | 28 mm    |
| L          | 1036 mm  |
| L2         | 996 mm   |
| L3         | 154 mm   |
| Y1         | 90 mm    |
| Valve type | SW       |

Permissible dimensional tolerances for elastomer parts according to DIN ISO 3302-1 M3 Note: Two ejectors/silencer box covers are used for the 1,234 mm and 1,432 mm lengths. Type FXP requires compressed air hose 12/9 mm

### Technical Data

| Attribute   | Value |
|-------------|-------|
| Arrangement | 5R36  |

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P


Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>

|                            |                                  |
|----------------------------|----------------------------------|
| Number of suction cells    | 137                              |
| Suction force at -250 mbar | 350 N                            |
| Suction rate (max.)        | 2270 l/min                       |
| Air consumption            | 625 l/min                        |
| Sealing element            | Suction Cups                     |
| Add. function              | 2x control valve vacuum/blow-off |
| Weight                     | 6.50 kg                          |
| Product family             | FXP                              |

Sound level: 74 dB(A) Max. degree of evacuation 55%

### Accessories



#### FLAN-PL 120x85x10 ST FLGR

Part no...:10.01.10.05701

Length L: 120 mm

Width B: 85 mm

Height H: 10 mm

Material: Steel

Construction use: Vacuum area gripping system



#### FLK G1/2-IG G1/2-AG

Part no...:10.01.03.00175

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### FST-FLEX 25 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05697

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



### FST-FLEX 25 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05695

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



### FST-FLEX 50 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05687

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### FST-FLEX 50 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05168

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



### FST-FLEX 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05698

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



### FST-FLEX 75 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05696

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### FST-STARR 25 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05810

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



### FST-STARR 25 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05806

Spring stroke Z: 25 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



### FST-STARR 50 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05809

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### FST-STARR 50 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05805

Spring stroke Z: 50 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section



### FST-STARR 75 HD1 G1/2-AG G3/8-IG

Part no...:10.01.10.05808

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 1 spring plunger

Construction use: Mounting section



### FST-STARR 75 HD2 G1/2-AG G3/8-IG

Part no...:10.01.10.05803

Spring stroke Z: 75 mm

Shape mounting elements: Heavy Duty 2 spring plunger

Construction use: Mounting section

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### MOD-FLAN 120x120 FXP-FMP

Part no...:10.01.21.00244

Length L: 120 mm

Width B: 120 mm

Height H: 60 mm

Weight: 1.1 kg

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



### MOD-FLAN 176.6x118 FXP

Part no...:10.01.38.01722

Length L: 176.6 mm

Width B: 118 mm

Height H: 40 mm

Construction use: Vacuum area gripping system FXP



### VS-MONT 84x21x34.5 VSi-V FXP

Part no...:10.01.38.02691

Length L: 84 mm

Width B: 21 mm

Height H: 34.5 mm

Construction use: Vacuum area gripping system FXP

with: vacuum switch VSi

## Contact Schmalz


Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### SET fuer-Sensor(FXP/FMP)

Part no...:10.01.38.01194



### SET FXC-FMC

Part no...:10.01.21.01291

Length L: 119 mm

Width B: 119 mm

Height H: 9.6 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



### SET FXP-FMP

Part no...:10.01.21.02407

Length L: 232 mm

Width B: 119 mm

Height H: 119 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### SET FXP-FMP 4NUTSTEIN

Part no...:10.01.21.00243

contains: 4 slot nuts

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP



### VAM 40 V U BAR

Part no...:10.07.02.00046

External diameter D: 40 mm

Measuring range: -1,00 ... 0,00 bar



### VSL 12-9 PU MI-TR

Part no...:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

## Contact Schmalz


Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### NUT-STEI 20x20 M8-IG 10

Part no...:25.09.06.00012

Width B: 20 mm

Height H: 4.9 mm

Material: Steel

Length L: 20 mm

Thread G1: M8-F

Shape mounting elements: With step

Surface: galvanised

Weight: 15.9 g



### NUT-STEI 20x20 M6-IG 10

Part no...:25.09.06.00036

Width B: 20 mm

Height H: 5 mm

Material: Steel

Length L: 20 mm

Thread G1: M6-F

Shape mounting elements: With step

Surface: galvanised



### ABDK-PROF-10x7x1450-KU-SW-FXP-FMP

Part no...:26.07.03.00002

Length L: 1,450 mm

Width B: 10 mm

Height H: 7 mm

Material: Plastics

Measuring range: bar

Construction use: Vacuum area gripping system FXP-FMP

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### ASK B-M12-5 5000 K-5P

Part no...:21.04.05.00080

Electrical connection: Fem connect M12, 5 pol

Cable length: 5,000 mm

Material hose: PUR cable



### FLAN-PL 120x120x10 FXC-FMC

Part no...:10.01.21.00313

Length L: 120 mm

Width B: 120 mm

Height H: 10 mm

Measuring range: bar

Construction use: Vacuum area gripping system FXC-FMC



### FLK G1/2-IG G1/2-AG V

Part no...:10.01.03.00207

Thread G1: G1/2"-F

Thread G2: G1/2"-M

Operating temperature: 0 ... 70 °C

Shape mounting elements: Reinforced

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### VS-MONT 76.5x19 VSi FXP-FMP

Part no...:10.01.38.02485

Length L: 76.5 mm

Width B: 19 mm

Add. function: Vacuum and pressure switch VSi

Measuring range: bar

Add. function: Vacuum and pressure switch

Construction use: Vacuum area gripping system FXP-FMP

## Spare parts



### ERS FXP-S-SEMP-75 DECKEL

Part no...:10.01.38.02191

Measuring range: bar

Size: SEMP-75

contains: Cover

Construction use: Vacuum area gripping system FXP-S



### ERS FXP-S-SEMP-50 DECKEL

Part no...:10.01.38.02190

Measuring range: bar

Size: SEMP-50

contains: Cover

Construction use: Vacuum area gripping system FXP-S

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Area Gripper

FXP-S-SW90 1036 5R36 SPB2-20-P

Part no...:10.01.38.03109

<https://www.schmalz.com/10.01.38.03109>



### MASK-FOL SW90 996 5R36 FXP-FMP

Part no...:10.01.38.03097

Length L: 996 mm

Width B: 109.8 mm

Height H: 0.4 mm

Measuring range: bar

Nozzle diameter: 0.9 mm

Construction use: Vacuum area gripping system FXP-FMP



### SD 120x79x29 FXP

Part no...:10.01.38.01607

Length L: 120 mm

Width B: 79 mm

Height H: 29 mm

Construction use: Vacuum area gripping system FXP



### SPB2 20 SI-40 P

Part no...:10.01.06.03125

Size: 20

Suction cup material: Silicone SI

Material hardness [Shore A]: 40 Shore A

Number of folds: 2.5

Shape: Push In

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)