

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no.:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Generators > Compact Ejectors > Compact Ejectors SCPMb / SCPMc / SCPMi > SCPMc 07 S01 NC M8-6 PNP AAU

### Mini Compact Ejector with air-saving function and display with



Nozzle size: 0.7 mm

Connection: Hose D4(1)-D4(2)

Suction rate (max.): 15 l/min

Air consumption suction: 22 l/min

Sound level free: 70 dB(A)

Pressure range (operating pressure): 3.5 ... 6.0 bar

Max. vacuum: 870 mbar


Electrical connection: Male connect M8, 6 pole

Construction shape vacuum switch: PNP switching

Control valve: Normally closed

Protection type IP: IP 40

### Design Data



| Attribute | Value    |
|-----------|----------|
| B         | 12 mm    |
| B1        | 12.50 mm |
| D         | 9 mm     |
| d1        | 4.20 mm  |
| d2        | 4.20 mm  |
| d4        | 4.30 mm  |
| G3        | M8x1-M   |
| H         | 65.30 mm |
| H1        | 73.90 mm |
| H2        | 24.95 mm |
| H3        | 7.50 mm  |
| H4        | 30 mm    |
| H5        | 7.50 mm  |
| H6        | 17.50 mm |
| L         | 76.50 mm |
| L1        | 95.30 mm |
| L2        | 11.40 mm |
| L3        | 20.50 mm |
| X1        | 36 mm    |

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no.:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>

### Technical Data

| Attribute                                     | Value           |
|-----------------------------------------------|-----------------|
| Nozzle size                                   | 0.70 mm         |
| Construction shape vacuum switch              | PNP switching   |
| Control valve                                 | NC              |
| Electrical connection                         | M8-6            |
| Degree of evacuation                          | 87 %            |
| Suction rate (max.)                           | 15 l/min        |
| Air consumption suction                       | 22 l/min        |
| Max. air consumption blow off                 | 10 l/min        |
| Max. vacuum                                   | 870 mbar        |
| Pressure optimal                              | 4 bar           |
| Pressure range (operating pressure)           | 3.5 ... 6.0 bar |
| Recomm. internal hose diameter compressed air | 2 mm            |
| Recomm. internal hose diameter vacuum         | 2 mm            |
| Operating temperature                         | 0 ... 50 °C     |
| Weight                                        | 84 g            |
| Product family                                | SCPMc           |

### Accessories



#### ASK WB-M8-6 2000 K-6P

Part no.:21.04.05.00488

Cable length: 2,000 mm

Material hose: PUR cable

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no.:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>



### ASK WB-M8-6 2000 S-M12-5

Part no.:21.04.05.00489

Cable length: 2,000 mm

Material hose: PUR cable



### ASK B-M8-6 5000 K-6P

Part no.:21.04.05.00255

Electrical connection: Fem connect M8, 6 pol

Cable length: 5,000 mm

Material hose: PUR cable



### ASV SCPMi B-M8-6 2xS-M12-4

Part no.:10.02.02.05602

Electrical connection: Fem connect M8, 6 pol

Length L: 1,000 mm

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no...:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>



### SD 10.5x31.7 SCPM

Part no...:10.02.02.05807

External diameter D: 10.5 mm

Length L: 31.7 mm

Construction use: SCPM



### ABL-SET SCPMi/c/b

Part no...:10.02.02.06080

Construction use: SCPMi/c/b



### SET SCPM MOUNT1

Part no...:10.02.02.05805

Thread G1: M4-M

Length L: 50 mm

Construction use: SCPM

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no...:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>



### BEF-WIN 15x50x36.1 1.5 SCPM

Part no...:10.02.02.05824

Length L: 36.1 mm

Construction use: SCPM



### STV-GE M5-AG 4

Part no...:10.08.02.00468

Thread G1: M5-M

Hose diameter: 4 mm

Material: Brass

Operating temperature: °C

External diameter D: 7.9 mm

Length L: 15 mm



### STV-GE M7-AG 6

Part no...:10.08.02.00469

Thread G1: M7-M

Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

External diameter D: 9.9 mm

Length L: 18.5 mm

## Mini compact ejector

SCPMc 07 S01 NC M8-6 PNP AAU

Part no...:10.02.02.05742

<https://www.schmalz.com/10.02.02.05742>



### ADP-G M7-IG 10.8x7.9 SCPMi/c/b

Part no...:10.02.02.05522

External diameter D: 10.8 mm

Thread G1: M7-F

Length L: 7.9 mm

Construction use: SCPMi/c/b



### ADP-G M5-IG 10.5x8.6 SCPMi/c/b

Part no...:10.02.02.05643

External diameter D: 10.5 mm

Thread G1: M5-F

Length L: 8.6 mm

Construction use: SCPMi/c/b

## Spare parts



### SD-EINS 6.4x21.8 SCPMi/c/b

Part no...:10.02.02.05403

Construction use: Mini compact ejector SCPMi/c/b

External diameter D: 6.4 mm

Length L: 21.8 mm

## Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)