

Plug union, elbow

STV-W G1/4-AG 12

Part no.:10.08.02.00162

<https://www.schmalz.com/10.08.02.00162>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-W G1/4-AG 12

Push-in Fitting, swivelling elbow



Thread G1: G1/4"-M


Hose diameter: 12 mm

Material: Nickel plated

Operating temperature: -20 ... 80 °C

Length L: 34.5 mm

Design Data



Attribute	Value
d	12 mm
G1	G1/4"-M
dn	8.50 mm
D1	19.80 mm
H	17 mm
H1	27 mm
L	34.50 mm
L1	44.50 mm
LG1	7.50 mm
SW1	17 mm
SW3	20 mm

Technical Data

Attribute	Value
Hose type	Hose D = 12 d = 9
Hose type	12-9
Material	Nickel plated
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	90 g

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Plug union, elbow

STV-W G1/4-AG 12

Part no.:10.08.02.00162

<https://www.schmalz.com/10.08.02.00162>

Product family

STV

Accessories



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at