


Flexible suction cup mounting for adaptation to sloping surfaces



- Thread G1: G1/2"-F
- Thread G2: G1/2"-M
- Operating temperature: 0 ... 70 °C
- Shape mounting elements: Reinforced

Design Data



Attribute	Value
dn	6 mm
G1	G1/2"-F
G2	G1/2"-M
L	53 mm
LG1	14 mm
LG2	14 mm
SW1	36 mm
W	8 °

Technical Data

Attribute	Value
Bending moment	65 Nm
Vertical load	4500 N
Weight	190 g
Product family	FLK