

Vacuum hose (meter)

VSL 42-32 PU-DS-AS TR

Part no.:10.07.09.00036

<https://www.schmalz.com/10.07.09.00036>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 42-32 PU-DS-AS TR

Hose for vacuum and compressed-air systems



External diameter D: 42 mm

Internal diameter d: 32 mm

Length max.: 20 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 25 mm

Pressure range (operating pressure): -1.00 ... 3.77 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	32 mm
D	42 mm

Technical Data

Attribute	Value
Hose type	42-32
Pressure range (operating pressure)	-1.00 ... 3.77 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	25 mm
Length max.	20 m
Weight/Meter	440 g/m
Weight/Meter	0.44 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Vacuum hose (meter)

VSL 42-32 PU-DS-AS TR

Part no.:10.07.09.00036

<https://www.schmalz.com/10.07.09.00036>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



SSD 37-42 ST-VZ

Part no.:10.07.10.00019

Clamping range: 37.0 ... 42.0 mm

Material: Steel

Surface: galvanised



ST G1-AG 32 MS-V

Part no.:10.08.03.00168

Thread G1: G1"-M

Hose diameter (rec.) d: 32 mm

Material: Brass

Surface: nickel plated

Length L: 10.5 mm

Nominal diameter dn: 26 mm

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Vacuum hose (meter)

VSL 42-32 PU-DS-AS TR

Part no...:10.07.09.00036

<https://www.schmalz.com/10.07.09.00036>



ST G1-1/4-AG 32 MS-V

Part no...:10.08.03.00169

Thread G1: G1-1/4"-M

Hose diameter (rec.) d: 32 mm

Material: Brass

Surface: nickel plated

Length L: 10.3 mm

Nominal diameter dn: 27.9 mm