

## Plug union, T

STV-T G1/8-AG 6

Part no.:10.09.02.00040

<https://www.schmalz.com/10.09.02.00040>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > STV-T G1/8-AG 6

### Push-in Fitting, T



Thread G1: G1/8"-M


Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41.5 mm

### Design Data



| Attribute | Value    |
|-----------|----------|
| d         | 6 mm     |
| G1        | G1/8"-M  |
| dn        | 4 mm     |
| D1        | 12 mm    |
| H         | 14 mm    |
| H1        | 20 mm    |
| L         | 41.50 mm |
| LG1       | 5.50 mm  |
| SW1       | 13 mm    |

### Technical Data

| Attribute                           | Value            |
|-------------------------------------|------------------|
| Hose type                           | Hose D = 6 d = 4 |
| Hose type                           | 6-4              |
| Material                            | Brass            |
| Pressure range (operating pressure) | bar              |
| Operating temperature               | °C               |
| Weight                              | 35.40 g          |
| Product family                      | STV              |

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)

## Plug union, T

STV-T G1/8-AG 6

Part no.:10.09.02.00040

<https://www.schmalz.com/10.09.02.00040>

### Accessories



#### VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



#### VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



#### VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

### Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | [schmalz@schmalz.at](mailto:schmalz@schmalz.at)