

Hose sleeve

ST G1/4-AG 13 MS-V

Part no.:10.08.03.00158

<https://www.schmalz.com/10.08.03.00158>

Home > Accessories for Screw Unions > ST G1/4-AG 13 MS-V

Hose sleeve



Thread G1: G1/4"-M

Hose diameter (rec.) d: 13 mm


Material: Brass

Surface: nickel plated

Length L: 5.5 mm

Nominal diameter dn: 7.5 mm

Design Data



Attribute	Value
dn	7.50 mm
D	13.90 mm
G1	G1/4"-M
L	5.50 mm
L1	42 mm
LG1	10 mm
SW1	17 mm

Technical Data

Attribute	Value
Material	Brass
Weight	32 g

Accessories

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Hose sleeve

ST G1/4-AG 13 MS-V

Part no.:10.08.03.00158

<https://www.schmalz.com/10.08.03.00158>



VSL 19-13 PVC-DS KL-TR

Part no.:10.07.09.00016

External diameter D: 19 mm

Internal diameter d: 13 mm


Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 85 mm

Pressure range (operating pressure): -0.90 ... 5.00 bar

Operating temperature: -15 ... 65 °C



VSL 21-12 PVC-G KL-TR

Part no.:10.07.09.00006

External diameter D: 21 mm

Internal diameter d: 12 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C