

Plug connector, T

SVB-T 10

Part no.:10.09.02.00025

<https://www.schmalz.com/10.09.02.00025>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > SVB-T 10

Plug connection, T




Hose diameter: 10 mm

Material: Brass

Operating temperature: -20 ... 80 °C

Length L: 55.5 mm

Design Data



Attribute	Value
d	10 mm
D1	16.70 mm
H	27.70 mm
H1	36 mm
L	55.50 mm

Technical Data

Attribute	Value
Hose type	Hose D = 10 d = 7
Hose type	10-7
Material	Brass
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	59 g
Product family	STV

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Plug connector, T

SVB-T 10

Part no.:10.09.02.00025

<https://www.schmalz.com/10.09.02.00025>

Accessories



VSL 10-7 PE MI-TR

Part no.:10.07.09.00083

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PE

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -30 ... 70 °C



VSL 10-7 PU MI-TR

Part no.:10.07.09.00084

External diameter D: 10 mm

Internal diameter d: 7 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 60 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -40 ... 85 °C