

Vacuum hose (meter)

VSL 87-75 PU-DS-AS

Part no.:10.07.09.00061

<https://www.schmalz.com/10.07.09.00061>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Vacuum / Compressed Air Hoses VSL > VSL 87-75 PU-DS-AS

Hose for vacuum and compressed-air systems



External diameter D: 87 mm

Internal diameter d: 75 mm

Length max.: 15 m

Material hose: PU, wire spiral, antistatic

Bending radius min.: 195 mm

Pressure range (operating pressure): -1.00 ... 2.36 bar

Operating temperature: -40 ... 90 °C

Design Data



Attribute	Value
d	75 mm
D	87 mm

Technical Data

Attribute	Value
Hose type	87-75
Pressure range (operating pressure)	-1.00 ... 2.36 bar
Operating temperature	-40 ... 90 °C
Bending radius min.	195 mm
Length max.	15 m
Weight/Meter	1460 g/m
Weight/Meter	1.46 kg/m
Material hose	PU, wire spiral, antistatic

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Vacuum hose (meter)

VSL 87-75 PU-DS-AS

Part no.:10.07.09.00061

<https://www.schmalz.com/10.07.09.00061>

Product family

VSL

Note: Operating pressure: In reference to media and ambient temperature of + 20 °C Min. bending radius: Referred to the inner side of the hose bend in a static state Max. length: Please indicate the tube length when placing the order!

Accessories



SSD 85-90 ST-VZ

Part no.:10.07.10.00102

Clamping range: 85.0 ... 90.0 mm

Material: Steel

Surface: galvanised