

Suction cup (round)

SAUG-SCGS 30 NBR-ESD-55

Part no...:10.01.30.00876

<https://www.schmalz.com/10.01.30.00876>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Flow Grippers > Suction Cups for Flow Grippers SCGS > SAUG-SCGS 30 NBR-ESD-55

Suction cup (round)




Size: 30

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
D1	31 mm
Dmax (N)	25 mm
Dmax(S)	31.50 mm
dn	12 mm
Ds	30.20 mm
G1	M20x1-F
H	24.10 mm
LG1	5 mm
Z (Stroke)	2.80 mm

Technical Data

Attribute	Value
Size	30
Suction cup material	Nitrile rubber NBR-ESD
Material hardness [Shore A]	55 Shore A
Product family	SAUG-SCGS

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Suction cup (round)

SAUG-SCGS 30 NBR-ESD-55

Part no.:10.01.30.00876

<https://www.schmalz.com/10.01.30.00876>

Spare parts



FLSA 30 NBR-ESD-55

Part no.:10.01.06.04214

Size: 30

Suction cup material: Nitrile rubber NBR-ESD

Material hardness [Shore A]: 55 Shore A