

Holder system

HTS-A3 EW SGM-HP 40x121 OP

Part no.:10.01.17.00590

<https://www.schmalz.com/10.01.17.00590>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > Holder System Magnetic Grippers
SGM-HP/-HT (Multiple) > HTS-A3 EW SGM-HP 40x121 OP

Holder system




Connection 1: Ball head 28.5 mm

Construction use: SGM-HP

Size: 40x121

Design Data



Attribute	Value
B	40 mm
D	28.50 mm
d	6.40 mm
H	9.40 mm
H1	48.30 mm
H2	4.50 mm
H4	35 mm
L	72 mm
X1	60 mm
Y1	16 mm
Y2	30 mm

Technical Data

Attribute	Value
Size	40x121
Material	Aluminum
Weight	114.60 g
Shape	End wall

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Holder system

HTS-A3 EW SGM-HP 40x121 OP

Part no...:10.01.17.00590

<https://www.schmalz.com/10.01.17.00590>

Accessories



HTR-UNI 2N X3

Part no...:10.01.03.00302

Suction cup connection: ball head 28.5 mm

Operating temperature: °C

Cross-beam connection: 2 T-slots