

Friction ring

REIB-RING SGM 70 PU-55

Part no.:10.01.17.00139

<https://www.schmalz.com/10.01.17.00139>

Home > Vacuum Technology for Automation > Vacuum Components > Special Grippers > Magnetic Grippers > REIB-RING SGM 70 PU-55

Friction ring




Construction use: Magnetic gripper

Size: 70

External diameter D: 68 mm

Internal diameter d: 51 mm

Design Data



Attribute	Value
D	68 mm
L	8.80 mm

Technical Data

Attribute	Value
Size	70
Suction cup material	Polyurethane PU
Operating temperature (max.)	100 °C
Material hardness [Shore A]	55 Shore A
Weight	11.60 g

Material HT2: Operating temperature max. short-term up to +250 °C

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at