

Plug union, T

STV-T G1/4-AG 6

Part no.: 10.09.02.00042

<https://www.schmalz.com/10.09.02.00042>

Home > Screw in Push Fittings > STV-T G1/4-AG 6

Push-in Fitting, T



Thread G1: G1/4\"-M


Hose diameter: 6 mm

Material: Brass

Operating temperature: °C

Length L: 41 mm

Design Data



Attribute	Value
d	6 mm
G1	G1/4\"-M
dn	4 mm
D1	11.30 mm
H	12.60 mm
H1	18.40 mm
L	41 mm
LG1	7.60 mm
SW1	17 mm

Technical Data

Attribute	Value
Hose type	Hose D = 6 d = 4
Hose type	6-4
Material	Brass
Pressure range (operating pressure)	bar
Operating temperature	°C
Weight	32.50 g
Product family	STV

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Plug union, T

STV-T G1/4-AG 6

Part no.:10.09.02.00042

<https://www.schmalz.com/10.09.02.00042>

Accessories



VSL 6-4 PE BL

Part no.:10.07.09.00014

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 6-4 PTFE MI-TR

Part no.:10.07.09.00157

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 50 m

Material hose: Polytetrafluorethylene

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -190 ... 260 °C



VSL 6-4 PU MI-TR

Part no.:10.07.09.00002

External diameter D: 6 mm

Internal diameter d: 4 mm

Length max.: 500 m

Material hose: PU

Bending radius min.: 35 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at