

Flat suction cup (round)

SGPN 24 SI-50 M5-AG

Part no.:10.01.01.11986

<https://www.schmalz.com/10.01.01.11986>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Flat Suction Cups SGPN > SGPN 24 SI-50 M5-AG

Flat suction cup (round) for careful gripping of paper, plastic film, etc.



Size: 24

Suction cup material: Silicone SI


Material hardness [Shore A]: 50 Shore A

Nipple material: Aluminum

Material characteristics: FDA

Vacuum connection: M5-M

Design Data



Attribute	Value
dn	2.50 mm
Dmax(S)	25.50 mm
Ds	24 mm
G1	M5-M
H	15.80 mm
LG1	5 mm
SW1	7 mm
Z (Stroke)	1.70 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	11 N
Volume	0.85 cm ³
Hose diameter (rec.) d	4 mm
Size	24
Number of folds	0
Suction cup material	Silicone SI
Material hardness [Shore A]	50 Shore A

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction cup (round)

SGPN 24 SI-50 M5-AG

Part no.:10.01.01.11986

<https://www.schmalz.com/10.01.01.11986>

Weight	2.10 g
Product family	SGPN

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Spare parts



SA-NIP N016 M5-AG DN250

Part no.:10.01.06.00123

Nipple family: N 016

Thread G1: M5-M

Length L1: 16 mm

Fitting length: 5 mm

Nominal diameter dn: 2.5 mm

Material: Aluminum



SGP 24 SI-50 N016

Part no.:10.01.01.10577

Size: 24

Suction cup material: Silicone SI

Material hardness [Shore A]: 50 Shore A