

Flat suction pad (round)

SFF 25 EPDM-45 G1/8-IG

Part no.:10.01.01.14267

<https://www.schmalz.com/10.01.01.14267>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 25 EPDM-45 G1/8-IG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces




Size: 25

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Design Data



Attribute	Value
Dmax(S)	26.50 mm
Ds	25 mm
dn	4 mm
G1	G1/8-IG
LG1	8 mm
H	27.20 mm
SW1	14 mm
Z (Stroke)	1.70 mm

Technical Data

Attribute	Value
Suction force (-600mbar)	18.50 N
Volume	1.20 cm ³
Size	25
Number of folds	0
Suction cup material	EPDM
Material hardness [Shore A]	45 Shore A
Weight	7.10 g
Product family	SFF

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction pad (round)

SFF 25 EPDM-45 G1/8-IG

Part no.:10.01.01.14267

<https://www.schmalz.com/10.01.01.14267>

Spare parts



SFF 25 EPDM-45 SC040

Part no.:10.01.01.14047

Size: 25

Suction cup material: EPDM

Material hardness [Shore A]: 45 Shore A

Number of folds: 0



SC 040 G1/8-IG

Part no.:10.01.06.02482

Connection geometry: 040

Connection: G1/8"-F

Length L1: 20.7 mm

Fitting length: 14 mm

Nominal diameter dn: 4.1 mm

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at