

Flat suction pad (round)

SFF 10 HT1-60 M5-AG

Part no.:10.01.01.14272

<https://www.schmalz.com/10.01.01.14272>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Plastic Films and Paper > Suction Cups SFF / SFB1 > SFF 10 HT1-60 M5-AG

Flat suction cup (round) for dynamic handling of thin and flexible workpieces




Size: 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0

Design Data



Attribute	Value
G1	M5-M
Dmax(S)	11 mm
Ds	10 mm
dn	1.80 mm
LG1	4.70 mm
H	15.40 mm
SW1	8 mm
Z (Stroke)	0.70 mm

Technical Data

Attribute	Value
Size	10
Suction cup material	High temperature material HT1
Suction force (-600mbar)	2.70 N
Product family	SFF
Volume	0.25 cm ³
Number of folds	0
Material hardness [Shore A]	60 Shore A

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at

Flat suction pad (round)

SFF 10 HT1-60 M5-AG

Part no.:10.01.01.14272

<https://www.schmalz.com/10.01.01.14272>

Spare parts



SFF 10 HT1-60 SC030

Part no.:10.01.01.14050

Size: 10

Suction cup material: High temperature material HT1

Material hardness [Shore A]: 60 Shore A

Number of folds: 0



SC 030 M5-AG

Part no.:10.01.06.02802

Connection geometry: 030

Connection: M5-M

Length L1: 15.5 mm

Fitting length: 5 mm

Nominal diameter dn: 1.8 mm