

Manuel slide valve

HSV 12 3/2 G1/2-IG S

Part no.:10.05.07.00037

<https://www.schmalz.com/10.05.07.00037>

Home > Vacuum Technology for Automation > Vacuum Components > Valve Technology > Manual Valves > Manual Slide Valves HSV > HSV 12 3/2 G1/2-IG S

Manual slide valve for manual switching of vacuum and compressed air



Nominal size: 12 mm


Function: 3/2-way valve

Thread G1: G1/2"-F

Pressure range (operating pressure): -0.95 ... 10.00 bar

with: Barrier

Design Data



Attribute	Value
D1	38 mm
G1	G1/2"-F
L	99.50 mm
LG1	15 mm
SW1	27 mm

Technical Data

Attribute	Value
Nominal size	12 mm
Nominal flow rate	16 m ³ /h
Nominal flow rate	266.70 l/min
Weight	0.36 kg
Product family	HSV

Contact Schmalz

Schmalz GmbH | Commerz Park West 1, 4061 Pasching, Austria | +43 7229 24 24 4 | schmalz@schmalz.at