

Flat suction cup (round)

PFG 15 NBR-55 N005

Part no.:10.01.01.00011

<https://www.schmalz.com/10.01.01.00011>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Round) > PFG 15 NBR-55 N005

Flat suction cup (round) for smooth or slightly rough surfaces




Size: 15

Suction cup material: Nitrile rubber NBR

Material hardness [Shore A]: 55 Shore A

Design Data



Attribute	Value
d	4.50 mm
d1	7.80 mm
Dk	12.20 mm
Dmax(S)	17.50 mm
Ds	15 mm
H	8 mm
H2	2.60 mm
Z (Stroke)	1.90 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	9 N
Volume	0.43 cm ³
Curve radius (min) (convex)	12.50 mm
Size	15
Nipple family	N 005
Suction cup material	Nitrile rubber NBR
Material hardness [Shore A]	55 Shore A
Weight	0.70 g

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Flat suction cup (round)

PFG 15 NBR-55 N005

Part no.:10.01.01.00011

<https://www.schmalz.com/10.01.01.00011>

Product family

PFG

Note: Suction force: The specified suction forces are theoretical values at a vacuum of -0.6 bar and with a dry, smooth and flat workpiece surface - they do not include a safety factor Hose diameter: The recommended hose diameter refers to a hose length of approx. 2 m

Accessories



SA-NIP N005 G1/8-AG DN200

Part no.:10.01.01.03529

Nipple family: N 005

Thread G1: G1/8"-M

Length L1: 17.5 mm

Length L: 5 mm

Fitting length: 5 mm

Nominal diameter dn: 2 mm

Material: Aluminum



SA-NIP N005 G1/8-IG DN200

Part no.:10.01.01.03521

Nipple family: N 005

Thread G1: G1/8"-F

Length L1: 20.5 mm

Length L: 16 mm

Fitting length: 16 mm

Nominal diameter dn: 2 mm

Material: Aluminum

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au