

Plug connector, T

SVB-T 12

Part no.:10.09.02.00023

<https://www.schmalz.com/10.09.02.00023>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Screw in Push Fittings > SVB-T 12

Plug connection, T




Hose diameter: 12 mm

Material: Brass

Operating temperature: -20 ... 80 °C

Length L: 69 mm

Design Data



Attribute	Value
d	12 mm
D1	19.90 mm
H	34 mm
H1	44 mm
L	69 mm

Technical Data

Attribute	Value
Hose type	Hose D = 12 d = 9
Hose type	12-9
Material	Brass
Pressure range (operating pressure)	-0.95 ... 15.00 bar
Operating temperature	-20 ... 80 °C
Weight	115 g
Product family	STV

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Plug connector, T

SVB-T 12

Part no.:10.09.02.00023

<https://www.schmalz.com/10.09.02.00023>

Accessories



VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au