

Flat suction cup (oval)

SGO 12x4 SI-HD-65 N020

Part no.:10.01.01.00222

<https://www.schmalz.com/10.01.01.00222>

Home > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Flat Suction Cups (Oval) > SGO 12x4 SI-HD-65 N020

Flat suction cup (oval) for narrow or curved workpieces




Dimensions (LxB): 12 x 4

Suction cup material: Silicone SI-HD

Material hardness [Shore A]: 65 Shore A

Design Data



Attribute	Value
Bmax(S)	5 mm
Bs	4 mm
d	4.20 mm
dn	1.50 mm
Dk	8 mm
Lmax(S)	13 mm
Ls	12 mm
H	15 mm
H2	9.30 mm
Z (Stroke)	0.50 mm

Note: Acceptable dimensional tolerances for elastomer parts concerning to DIN ISO 3302-1 M3

Technical Data

Attribute	Value
Suction force (-600mbar)	1.80 N
Dimensions (LxB)	12 x 4
Suction cup material	Silicone SI-HD
Material hardness [Shore A]	65 Shore A
Weight	0.50 g
Product family	SGO

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Flat suction cup (oval)

SGO 12x4 SI-HD-65 N020

Part no...:10.01.01.00222

<https://www.schmalz.com/10.01.01.00222>

Accessories



SA-NIP N020 M5-AG DN180

Part no...:10.01.01.00312

Thread G1: M5-M

Length L1: 15 mm

Fitting length: 3 mm

Nominal diameter dn: 1.8 mm

Material: Aluminum

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au