

Ball joint

KGL G1/8-IG G1/8-AG A2

Part no...:10.01.03.00109

<https://www.schmalz.com/10.01.03.00109>

Home > Vacuum Technology for Automation > Vacuum Components > Mounting Elements > Jointed Mountings > Ball Joints KGL > KGL G1/8-IG G1/8-AG A2

Suction cup mounting with joint for adaptation to sloping surfaces




Thread G1: G1/8"-F

Thread G2: G1/8"-M

Height H: 26.5 mm

Material: Aust. Stainless steel

Design Data



Attribute	Value
dn	2 mm
H	26.50 mm
G1	G1/8"-F
G2	G1/8"-M
LG1	8.50 mm
LG2	7 mm
SW1	14 mm
W	15 °

Technical Data

Attribute	Value
Vertical load	300 N
Weight	26 g
Product family	KGL

Spare parts

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Ball joint

KGL G1/8-IG G1/8-AG A2

Part no...:10.01.03.00109

<https://www.schmalz.com/10.01.03.00109>



DR G1/8 15/10x1.5 PA

Part no...:10.07.08.00020

for: G1/8

External diameter D: 15 mm

Internal diameter d: 10 mm

Material: Polyamide