

## Hose sleeve

ST G3/8-AG 9 MS-V

Part no.:10.08.03.00159

<https://www.schmalz.com/10.08.03.00159>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Accessories for Screw Unions > ST G3/8-AG 9 MS-V

### Hose sleeve



Thread G1: G3/8"-M

Hose diameter (rec.) d: 9 mm


Material: Brass

Surface: nickel plated

Length L: 6 mm

Nominal diameter dn: 7.4 mm

### Design Data



| Attribute | Value   |
|-----------|---------|
| dn        | 7.40 mm |
| D         | 8.50 mm |
| G1        | G3/8"-M |
| L         | 6 mm    |
| L1        | 43 mm   |
| LG1       | 10 mm   |
| SW1       | 19 mm   |

### Technical Data

| Attribute | Value |
|-----------|-------|
| Material  | Brass |
| Weight    | 31 g  |

### Accessories

#### Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | [schmalz@schmalz.com.au](mailto:schmalz@schmalz.com.au)

## Hose sleeve

ST G3/8-AG 9 MS-V

Part no.:10.08.03.00159

<https://www.schmalz.com/10.08.03.00159>



### VSL 12-9 PE BL

Part no.:10.07.09.00050

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 100 m

Material hose: PE

Pressure range (operating pressure): bar

Operating temperature: °C



### VSL 12-9 PU MI-TR

Part no.:10.07.09.00037

External diameter D: 12 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PU

Bending radius min.: 70 mm

Pressure range (operating pressure): -0.95 ... 10.00 bar

Operating temperature: -20 ... 90 °C



### VSL 15-9 PVC-G KL-TR

Part no.:10.07.09.00005

External diameter D: 15 mm

Internal diameter d: 9 mm

Length max.: 50 m

Material hose: PVC with tissue

Pressure range (operating pressure): bar

Operating temperature: °C

## Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | [schmalz@schmalz.com.au](mailto:schmalz@schmalz.com.au)