

Vacuum block

VCBL-R 160x160x150 30/50 TV

Part no...:10.01.12.03112

<https://www.schmalz.com/10.01.12.03112>

Home > Vacuum Clamping Technology > Clamping Equipment for Woodworking > Clamping Equipment for Grid Table Systems > Vacuum block
VCBL-R > VCBL-R 160x160x150 30/50 TV

Vacuum block for grid tables



Dimensions (LxB): 160 x 160

Length L: 160 mm

Width B: 160 mm


Height H: 150 mm

Grid: 30/50

Recommended slot width x slot depth [mm]: 6 x 7 mm

Add. function: Sensing valve

Design Data



Attribute	Value
B	160 mm
H	150 mm
L	160 mm
L1	160 mm

Technical Data

Attribute	Value
Grid	30/50

Spare parts

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Vacuum block

VCBL-R 160x160x150 30/50 TV

Part no...:10.01.12.03112

<https://www.schmalz.com/10.01.12.03112>



TV D9 4.3

Part no...:10.01.12.02514

External diameter D: 9 mm

Spring stroke Z: 4.3 mm

Length L: 22.8 mm



ERS VCBL-R Winkel

Part no...:10.01.12.02691



ERS VCBL-R

Part no...:10.01.12.02693

Contact Schmalz


Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Vacuum block

VCBL-R 160x160x150 30/50 TV

Part no...:10.01.12.03112

<https://www.schmalz.com/10.01.12.03112>



ISDR 150x150x13.5 R 30/50


Part no...:10.01.15.00352

Length L: 150 mm

Width B: 150 mm

Height H: 13.5 mm

Type: R 30/50



DR 188/180x6 MOS NK-20

Part no...:10.01.12.02901

External diameter D: 188 mm

Internal diameter d: 180 mm

Length L: 6 mm

Width B: 4 mm

Height H: 6 mm

Material type: Foam rubber

Sealing material: Natural Rubber NK

Material hardness [Shore A]: 20 Shore A

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au