

Hose clamp

SSB 40-60 ST-VZ

Part no...:10.07.10.00005

<https://www.schmalz.com/10.07.10.00005>

Home > Vacuum Technology for Automation > Vacuum Components > Filters and Connections > Hoses and Connections > Hose Clamps SSB / SSD > SSB 40-60 ST-VZ

Hose clamp for securing smooth hoses




Clamping range: 40.0 ... 60.0 mm

Material: Steel

Surface: galvanised

Design Data



Attribute	Value
d1	40 mm
d2	60 mm
L	9 mm

Technical Data

Attribute	Value
Clamping range	40.0 ... 60.0 mm
Material	Steel
Weight	25 g
Product family	SSB / SSD

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au

Hose clamp

SSB 40-60 ST-VZ

Part no.:10.07.10.00005

<https://www.schmalz.com/10.07.10.00005>

Accessories



KAPP 9 Band

Part no.:20.12.01.00036

Length L: 9 mm

Size: Band



VSL 41-32 PVC-DS KL-TR

Part no.:10.07.09.00008

External diameter D: 41 mm

Internal diameter d: 32 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 110 mm

Pressure range (operating pressure): -0.85 ... 4.00 bar

Operating temperature: -15 ... 65 °C



VSL 48-38 PVC-DS KL-TR

Part no.:10.07.09.00009

External diameter D: 48 mm

Internal diameter d: 38 mm

Length max.: 50 m

Material hose: PVC with wire spiral

Bending radius min.: 120 mm

Pressure range (operating pressure): -0.88 ... 7.00 bar

Operating temperature: -15 ... 65 °C

Contact Schmalz

Schmalz Australia Pty Ltd | 25 Turbo Drive, Bayswater North, VIC, 3153 Melbourne, Australia | +61 3 9215 8800 | schmalz@schmalz.com.au